



BWT connection kit 1 - 3 for
BWT PERMAQ® compact 2-4
BWT PERMAQ® compact 11-18
BWT pro-ro 4, 14, 18, 24, 26
Hose connection kits for compact RO units

**BWT connection kit 1 to 3
the highly flexible hose connections**

- Three professional hose kits for an easy installation of BWT compact reverse osmosis units
- Flexible PE hoses 8/6mm for permeate and concentrate with colour coding, at the *connection kit 1*
- Highly flexible silicone hose with braiding made of stainless steel for permeate and concentrate for PE hose 8/6mm, at the *connection kit 2*
- Highly flexible silicone hose with braiding made of stainless steel for feed water, at the *connection kits 1, 2 and 3*

**BWT connection kits for PERMAQ® compact 2-4 & 11-18
& pro-ro 4, 14, 18, 24, 26 – the perfect solution for:**

- Gastronomy
- Laboratory
- Air-conditioning technology
- Dental technology
- Mechanical engineering
- Drinking water

For You and Planet Blue.

BWT
BEST WATER TECHNOLOGY

BWT Hose connection kits for compact RO units

Technical data:				
Model name / type:		Connection Kit 1	Connection Kit 2	Connection Kit 3
Feed water:				
Hose type / length	- / mm	Silicone hose with braiding made of stainless steel; DN10, L= 1.500mm		
Connection adapter	inch / mm	2 x 3/4" union nut		
Permeate:				
Hose type / length	- / mm	PE, Ø8x1 mm, blue, L= 3.000mm	Silicone hose with braiding made of stainless steel; DN10, L= 1.500mm	Silicone hose with braiding made of stainless steel; DN10, L= 1.500mm
Connection adapter	inch / mm	Ø8mm plug connector	3/4" union nut - Ø8mm plug connector	2 x 3/4" union nut
Concentrate:				
Hose type / length	mm / mm	PE, Ø8x1 mm, black, 3.000mm		
Connection adapter	mm	Ø8mm plug connector		
Order No. (BWT water+more GmbH):		812761	812762	-
Order No. (Warewashing segment):		823006	823007	824046

Function description:

- Scope of application: flexible connection of the BWT compact reverse osmosis units

With the three different hose connection kits the operator of the BWT compact-reverse osmosis can connect his unit in a flexible and secure manner. The professional hose connection kits are specifically designed for the interfaces of the BWT compact reverse osmosis units.

Process safety and selection of the most decent hose set:

- Stress crack free and flexible connection
- Confusion-security by colour coding of the connection kit 1

Replacement of the connection hoses:

- The manufacturer BWT recommends a replacement of all connection hoses within a maintenance interval of 5 years.




Fig.1: Example overview of the hose connection kit 1, (1) feed water hose, (2) pure water hose, (3) concentrate hose